### MLI•17 CANopen

### Product overview

MDrive® Linear Actuators are compact linear motion systems. External or non-captive shaft linear mechanicals are integrated with stepper motor and electronics for reliable, repeatable motion. Customization is available for volume opportunities.

CANopen products integrate 1.8° 2-phase stepper motor linear actuator, motion controller and drive electronics, supporting CiA DS301 and DSP402 Device Profile for Drives and Motion Control. Options include encoder, and CANopen dongle MD-CC500-000 for product setup and testing.

MDrive product's precision rolled lead screws are manufactured from premium grade stainless steel with optional Teflon® coating. Designed specifically for motion control applications, our high quality screws deliver long life and quiet operation.

Simplify machine design and reduce assembly time by replacing multiple components with a single compact integrated motor. Fewer individual system components eliminates multiple potential failure points, and lowers risk of electrical noise by eliminating cabling between motor and drive.



MDrive Linear Actuator MLI•17 CANopen products: integrated NEMA17 motor, controls and mechanicals, non-captive and external shaft styles, IP20-rated

### Specifications

Communication	Protocol type		CANopen
Input power	Voltage	VDC	+12+48
	Current maximum (1)	Amp	2.0
Motor	Frame size	NEMA	17
		inches	1.7
		mm	42
	Length	stack size	single
Maximum thrust (2)	Non-captive shaft	lbs	50
		kg	22
	External shaft with	lbs	25
	general purpose nut	kg	11
	External shaft with anti-	lbs	5
	backlash nut	kg	2
Maximum	General purpose	inch	0.005
repeatability		mm	0.127
	Anti-backlash (3)	inch	0.0005
		mm	0.0127
Thermal	Operating temp	Heat sink maximum	85°C
	non-condensing	Motor maximum	100°C
Protection	Туре	IP rating	IP20
Motion	Microstep resolution	Number of settings	20
		Steps per revolution	200, 400, 800, 1000, 1600, 2000, 3200, 5000, 6400, 10000, 12800, 20000, 25000, 25600, 40000, 50000, 51200, 36000 (0.01 deg/µstep), 21600 (1 arc minute/µstep), 25400 (0.001mm/µstep)

(1) Actual power supply current will depend on voltage and load.
(2) Performance data for maximum force/load is based on a static load and will vary with a dynamic load.

(3) Only applicable for External shaft linear actuator with anti-backlash nut.




### MLI•17 CANopen

### Screws (1)

Screw lengths (2)	minimum	inches	3.0							
		mm	77.5							
	maximum	inches	18.0							
		mm	455.0							
Load limits (3)	non-captive shaft	lbs	50							
		kg	22							
	external shaft w/ general purpose nut	lbs	25							
		kg	11							
	external shaft w/ anti-backlash nut	lbs	5							
		kg	2							
End options	threaded	metric	M4 x 0.7 mm thread to within 0.03"/0.76 mm of shoulder							
		UNC	#8-32 UNC	C-2A thread to within 0.03"/0.76 mm of shoulder						
	smooth	inches	Ø 0.1967 ±	±0.001						
		mm	Ø 5 ±0.003	Ø 5 ±0.003						
	none		-							
Lead / pitch		travel	per rev	per full step						
	screw A	inches	0.250	0.00125						
		mm	6.350	0.0317						
	screw B	inches	0.125	0.00063						
		mm	3.175	0.0158						
	screw C	inches	0.063	0.00031						
		mm	1.588	0.0079						

- (1) Stainless steel rolled screws are corrosion resistant and non-magnetic, with Teflon coating available.
- (2) Standard 0.1" / 2.5mm screw length increments are available.
- (3) Performance data for maximum force/load is based on a static load and will vary with a dynamic load.

#### screw dimensions



#### end options



general nurnose nute






anti-hacklash nuts

### Nuts (4)

		general purpose nuts	anti-dackiash nuts
A	inches	0.50	0.50
	mm	12.7	12.7
В	inches max	0.75	0.9
	mm max	19.1	22.86
D	inches	1.0	1.0
	mm	25.4	25.4
E	inches	0.14	0.14
	mm	3.6	3.6
F	inches	0.15	0.18
	mm	3.81	4.57
BCD	inches	0.75	0.75
	mm	19.1	19.1
	lbs	25	5
	kg	11	2
		free wheeling	< 1.0 oz-in < 0.7 N-cm
	B D E	mm   inches max   mm max     D   inches   mm     E   inches   mm     F   inches   mm     BCD   inches   mm     BCD   inches   mm     Ibs	A inches 0.50 mm 12.7 inches max 0.75 mm max 19.1 inches 1.0 mm 25.4 inches 0.14 mm 3.6 inches 0.15 mm 3.81 inches 0.75 mm 19.1 lbs 25 kg 11

(4) External shaft MDrive Linear Actuators employ a nut which moves axially along the threaded shaft as the screw rotates. Two nut styles are available: general purpose and anti-backlash. While anti-backlash nuts provide higher accuracy and low drag torque, general purpose nuts are rated for higher load limits.









## MLI•17 CANopen


### **Dimensions**


inches (mm)













#### P1 connector options


12.00 (304.8)

12.00 (304.8)

12.01 (305.8)








www.motion.schneider-electric.com

## MLI•17 CANopen





PD16-1417-FL3

### Accessories

description	length feet (m)	part number
Communication converter Electrically isolated, in-line converter pre-wired with mating connector to conveniently set/program communication parameters for a single MDrive Plus via a PC's USB port.		
Interface cable for all CANopen products. Requires mating connector adapter for DB9 connector. Requires power supply, not supplied.	12.0 (3.6)	MD-CC500-000
Prototype development cable Speed test/development with pre-wired mating connector with other cable end open.		
Mates to 16-pin locking wire crimp connector for I/O, power and remote encoder option	10.0 (3.0)	PD16-1417-FL3
Mating connector kits Connectors for assembly of cables, cable material not supplied. Sold in lots of 5. Manufacturer's crimp tool recommended for crimp connectors.		
16-pin locking wire crimp connector for I/O, power and remote encoder option	_	CK-10
Drive protection module Limits surge current and voltage to a safe level when DC input power is switched on-and-off to an MDrive Plus.		
For all MDrive Plus linear actuator products	_	DPM75

### MLI•17 CANopen

### MDrive® 17 Plus IP20



### MDrive® 17 Plus<sup>2</sup> IP20









External shaft style

### Part numbers,

### IP20-rated products

example part number	М	L	Ι	1	F	С	В	1	7	Α	4 -	-EQ
MDrive Linear Actuator version MLI = Intelligent — CANopen	М	L	1	1	F	С	В	1	7	Α	4 -	-EQ
Input 1 = Plus version with standard features 3 = Plus² version with expanded features	М	L	I	1	F	С	В	1	7	Α	4 -	-EQ
P1 connector F = flying leads (1) P = pluggable (1) C = wire crimp (2)	М	L	I	1	F	С	В	1	7	Α	4 -	-EQ
Communication type C = CANopen	М	L	1	1	F	С	В	1	7	Α	4 -	-EQ
P2 connector B = DB9	М	L	1	1	F	С	В	1	7	Α	4 -	-EQ
Motor size 17 = NEMA 17 1.7" / 42mm	М	L	I	1	F	С	В	1	7	Α	4 -	-EQ
Motor length A = single stack	М	L	I	1	F	С	В	1	7	Α	4 -	-EQ
Drive voltage 4 = +12 to +48 VDC	М	L	1	1	F	С	В	1	7	Α	4 -	-EQ
Options — omit from part number if unwanted  -EQ = internal 512-line magnetic encoder w/ index mark  -EE (2) = remote differential encoder interface; encoder not supp	olied											-EQ

- (1) Only available with Plus products.
- (2) Only available with Plus<sup>2</sup> products.

### -• continued

example part number — linear actuator specifications	-L	Α	1	М	0	6	0	Z	Τ
Linear actuator -L	- L	Α	1	М	0	6	0	Z	Т
Screw lead/pitch by travel per rev A = 0.250" / 6.35mm B = 0.125" / 3.175mm C = 0.063" / 1.588mm	- L	Α	1	М	0	6	0	Z	T
Shaft style 1 = non-captive (3) 3 = external (4)	- L	Α	1	М	0	6	0	Z	Т
Screw end finish M = metric threaded U = UNC threaded S = smooth Z = none	- L	Α	1	M	0	6	0	Z	Т
Screw length (5) 030 = minimum 3.0" / 77.5mm 180 = maximum 18.0" / 455.0mm	-L	Α	1	М	0	6	0	Z	Т
Nut Z = none - for non-captive shaft products G = general purpose - for external shaft products A = anti-backlash - for external shaft products	-L	Α	1	М	0	6	0	Z	Т
Coating T = Teflon® Z = none	-L	A	1	М	0	6	0	Z	Т


- (3) Unsupported loads and side loading are not recommended.
- (4) Loads must be supported. Side loading is not recommended.
- (5) Screw lengths specified in 0.1" / 2.5mm increments.

### MLI•17 CANopen

### Motor performance

ML•17 NEMA 17 motor specifications	Motor		Stack length	Single			
	Holding torque		oz-in	29			
	Holding torque		N-cm	20			
	Deter inertie	Rotor inertia	Poter inertia OZ-in-Sec <sup>2</sup>				
	Rotor mertia		kg-cm <sup>2</sup>	0.034			
	Maight without corour		OZ	9.6			
	Weight without screw		g	272.2			
	Maximum screw misalignmen	nt	0	±1			
	Maximum thrust (1)	Non-captive shaft	lbs	50			
			kg	22			
		External shaft with general purpose nut	lbs	25			
			kg	11			
		External shaft with anti-backlash nut	lbs	5			
			kg	2			
	Maximum repeatability	General purpose	inch	0.005			
			mm	0.127			
		Anti-backlash (2)	inch	0.0005			
			mm	0.0127			

<sup>(1)</sup> Performance data for maximum force/load is based on a static load and will vary with a dynamic load. (2) Only applicable for External shaft linear actuator with anti-backlash nut.



Test conditions: maximum force/load is based on a static load. This will vary with a dynamic load.

Load limits - non-captive shaft: 50lbs/22kg - external shaft: determined by selected nut