# MDI•17 programmable Motion Control

### Product overview

MDrive® Plus Motion Control products integrate 1.8° 2-phase stepper motor, fully programmable motion controller, drive electronics and optional encoder. Products with encoders include stall detection, position maintenance, and find index mark.

Programming for these stand-alone motion control solutions is via RS-422/485 interface with MCode software using simple 1 to 2 character instructions.

### Application areas

MDrive Plus products deliver reliable performance for new and existing motion control applications. Satisfying the requirements for a wide range of machine builders.

Simplify your machine design and reduce cabinet size by replacing multiple components with a single compact integrated motor. Fewer individual system components eliminates multiple potential failure points, and lowers risk of electrical noise by eliminating cabling between motor and drive.

These compact, powerful and cost effective motion control solutions deliver exceptional smoothness and performance that can reduce system cost, design and assembly time for a large range of 2-phase stepper motor applications.



MDI•17 MDrive Plus programmable Motion Control products: integrated NEMA17 motor and controls, IP20 & IP65-rated

### General features

Compact integrated mic	rostepping drive, programmable motion controller and NEMA17 1.8° 2-phase stepper motor						
Advanced current control for exceptional performance and smoothness							
+12 to +48 VDC single supply							
20 microstep resolutions	up to 51,200 steps per rev including: Degrees, Metric, Arc Minutes						
Auxiliary logic power su	pply input						
0 to 5 MHz step clock rate selectable in 0.59 Hz increments							
Up to 8 I/O lines							
One 10 bit selectable analog input							
Communication	RS-422/485						
Protection	IP20, IP65 ratings						
Programmable	Motor run/hold current						
Available options	Motor stack lengths						
	Long life linear actuators (1)						
Up to 8 I/O lines           One 10 bit selectable analog input           Communication         RS-422/485           Protection         IP20, IP65 ratings           Programmable         Motor run/hold current           Available options         Motor stack lengths           Long life linear actuators (1)         Connector options           Encoders         Rear control knob for manual positioning	Connector options						
	Encoders						
20 microstep resolutions up to 51,200 steps per rev including: Degrees, Metric, Arc Minutes  Auxiliary logic power supply input  0 to 5 MHz step clock rate selectable in 0.59 Hz increments  Up to 8 I/O lines  One 10 bit selectable analog input  Communication RS-422/485  Protection IP20, IP65 ratings  Programmable Motor run/hold current  Available options Motor stack lengths  Long life linear actuators (1)  Connector options  Encoders							
Graphical user interface	provided for quick and easy parameter setup						

(1) Refer to MDrive Linear Actuator documentation.

# MDI•17 programmable Motion Control

### **Specifications**

Communication	Protocol type	RS-422/485	4.8 to 115.2 kbps baud rate
Input power	Voltage	VDC	+12+48
	Current maximum (1)	Amp	2.0
Motor	Frame size	NEMA	17
		inches	1.7
		mm	42
	Holding torque	oz-in	3275
		N-cm	23 53
	Length	stack sizes	1, 2 & 3
Thermal	Operating temp	Heat sink maximum	85°C
	non-condensing	Motor maximum	100°C
Protection	Туре	IP rating	IP20, IP65
		I/O warnings	Over temp, short circuit, transient, over voltage, inductive clamp
Auxiliary logic input	Voltage range		+12 to +24 VDC When input voltage is removed, maintains power only to control and feedback circuits.
Analog input	Resolution		10 bit
0 1	Voltage range		0 to +5 VDC, 0 to +10 VDC, 0-20 mA, 4-20 mA
General purpose I/O	Output sinking current		Up to 600 mA
1 100000	Plus products	Number	4
		Туре	Sourcing or sinking inputs, or sinking outputs
		Logic range	Inputs and outputs tolerant to +24 VDC, inputs TTL level compatible
	Plus <sup>2</sup> products	Number	8 or 4 (2)
		Туре	Sourcing or sinking outputs/inputs
		Logic range	Sourcing outputs +12 to +24 VDC, inputs and sinking outputs tolerant to +24 VDC, inputs TTL level compatible
Motion	Open loop configuration	Number of settings	20
Modeli	opon loop comigaration	Steps per revolution	200, 400, 800, 1000, 1600, 2000, 3200, 5000, 6400, 10000, 12800, 20000, 25000, 25600, 40000, 50000, 51200, 36000 (0.01 deg/µstep), 21600 (1 arc minute/µstep), 25400 (0.001mm/µstep)
	Counters	Туре	Position, encoder / 32 bit
	Coumbie	Edge rate maximum	5 MHz
	Velocity	Range	+/- 5,000,000 steps per second
	volcony	Resolution	0.5961 steps per second
	Accel/Decel	Range	1.5 to 10 <sup>9</sup> steps per second <sup>2</sup>
	7.0001120001	Resolution	90.9 steps per second <sup>2</sup>
	Position feedback	Optional	Encoder required
Expanded motion	Electronic gearing	Range	0.001 to 2.000
Plus <sup>2</sup> products only	external clock in (3)	Resolution	32 bit
		Threshold	TTL
	High speed I/O	Position capture	Input filter range 50 nS to 12.9 µS (10 MHz to 38.8 kHz)
	riigir opeda i/o	r contorr captare	Resolution 32 bit
		Trip output	Speed 150 nS
		тр оприс	Resolution 32 bit
			Threshold TTL
	Position feedback	Optional	Remote encoder interface required
Software	Program storage	Type/size	Flash/6384 bytes
Johnward	User registers	13000120	Four 32 bit
	User program labels & va	riahles	192
	Math functions	IIIADIOO	+, x, ÷, >, <, <=, >=, AND, OR, XOR, NOT
	Branch functions		Branch and Call
		Inpute	
	General purpose I/O functions	Inputs	home, limit plus, limit minus, go, stop, pause, jog plus, jog minus, general purpose
		Outputs	moving, fault, stall, velocity change, general purpose
	Trip functions		Trip on input, trip on position, trip on time, trip capture, trip on relative position
	Party mode addresses		62
	Encoder functions		Stall detection, position maintenance, find index

<sup>(1)</sup> Actual power supply current will depend on voltage and load.

<sup>(2)</sup> I/O is reduced from 8 to 4 for products with remote encoder option.


<sup>(3)</sup> Adjusting the microstep resolution can increase the range.

# MDI•17 programmable Motion Control

### **Dimensions**

### MDI-17 NEMA17 motor, IP20-rated






Motor stack length	Lmax	Lmax1 (1)	Lmax2
Single	2.20 (55.9)	2.45 (62.25)	2.79 (70.9)
Double	2.43 (61.7)	2.68 (68.05)	3.02 (76.7)
Triple	2.77 (70.4)	3.02 (76.75)	3.37 (85.6)

### P1 connector options





### P2 connector options







wire crimp – 10-pin friction lock


### (1) Grounding screw is not present on all products.



Lmax2 option

control knob - 20 in-lb

### MDI•17 NEMA17 motor, IP65-rated




Motor stack length	Lmax	Lmax2	Lmax3
Single	2.48 (62.71)	3.15 (79.72)	3.08 (77.95)
Double	2.71 (68.55)	3.38 (85.57)	3.31 (83.79)
Triple	3.05 (77.18)	3.72 (94.20)	3.65 (92.42)

www.motion.schneider-electric.com


### MDI•17 programmable Motion Control

# MDrive® Plus non-locking IDC mating connector in-line converter

MD-CC400-001



MD-CC402-001




MD-CC401-001



PD10-1434-FL3



PD16-1417-FL3



MD-CS100-000

### Accessories

` '	description   length   part number   feet (m)
-----	-----------------------------------------------

### QuickStart Kit

For rapid design verification, all-inclusive QuickStart Kits includes prototype development cables and a communication converter for MDrive Plus initial functional setup and system testing.

For all MDrive17 programmable Motion Control products	_	add "K" to part number

### Communication converter

Electrically isolated, in-line converter pre-wired with mating connector to conveniently set/program communication parameters for a single MDrive Plus via a PC's USB port.

Mates to 10-pin non-locking IDC connector	12.0 (3.6)	MD-CC400-001
Mates to 10-pin friction lock wire crimp connector	12.0 (3.6)	MD-CC402-001
Mates to 5-pin female M12 industrial connector	12.0 (3.6)	MD-CC401-001

### Prototype development cable

Speed test/development with pre-wired mating connector with other cable end open.

Mates to 10-pin locking wire crimp connector for I/O and remote encoder option	10.0 (3.0)	PD10-1434-FL3
Mates to 16-pin locking wire crimp connector for I/O, power and remote encoder option	10.0 (3.0)	PD16-1417-FL3
Mates to 19-pin male M23 industrial connector with straight termination for I/O, power and remote encoder option	13.0 (4.0)	MD-CS100-000
Mates to 19-pin male M23 industrial connector with right angle termination for I/O, power and remote encoder option	13.0 (4.0)	MD-CS101-000

### Mating connector kits

Connectors for assembly of cables, cable material not supplied. Sold in lots of 5. Manufacturer's crimp tool recommended for crimp connectors.

10-pin friction lock wire crimp connector for communication	_	CK-02
10-pin non-locking IDC connector for communication	_	CK-01
16-pin locking wire crimp connector for I/O, power and remote encoder option	_	CK-10

### Drive protection module

Limits surge current and voltage to a safe level when DC input power is switched on-and-off to an MDrive Plus.

input power to ewiteriou on una en te un menver ide.		
For all MDrive17 programmable Motion Control products	_	DPM75

## MDI•17 programmable Motion Control

### MDrive® 17 Plus IP20



### P1: I/O & Power

- F = 12" flying leads
  P = non-locking spring clamp terminal strip

### P2: Communication

- D = RS-422/485 with 10-pin IDC non-locking connector
- L = RS-422/485 with 10-pin friction lock wire crimp connector

### MDrive® 17 Plus<sup>2</sup> IP20



# P1: I/O & Power, and optional remote encoder

C = 16-pin locking wire crimp connector

### P2: Communication

- D = RS-422/485 with 10-pin IDC non-locking connector
- L = RS-422/485 with 10-pin friction lock wire crimp connector

### MDrive® 17 Plus<sup>2</sup> IP65 with industrial connectors



### P2: Communication

- Q = RS-422/485 with 5-pin M12 female industrial connector
- P1: I/O & Power, and optional remote encoder
- M =19-pin M23 male industrial connector

### Part numbers

### IP20-rated products

			_	_		_	_	_	_	_	_	_	
example part number	K	M	D	١	1	F	R	D	1	7	Α	4	–N
QuickStart Kit K = kit option, omit from part number if unwanted	K	М	D	Ι	1	F	R	D	1	7	Α	4	-N
MDI = Intelligent — programmable Motion Control	K	М	D	1	1	F	R	D	1	7	Α	4	-N
Input 1 = Plus version with standard features 3 = Plus² version with expanded features	K	М	D	I	1	F	R	D	1	7	Α	4	-N
P1 connector F = flying leads P = pluggable C = wire crimp (1)	K	М	D	I	1	F	R	D	1	7	Α	4	-N
Communication type R = RS-422/485	K	М	D	T	1	F	R	D	1	7	Α	4	-N
P2 connector D = IDC L = wire crimp	K	М	D	I	1	F	R	D	1	7	Α	4	-N
Motor size 17 = NEMA 17 1.7" / 42mm	K	М	D	I	1	F	R	D	1	7	Α	4	-N
Motor length A = single stack B = double stack C = triple stack	K	М	D	I	1	F	R	D	1	7	Α	4	-N
Drive voltage 4 = +12 to +48 VDC	K	М	D	I	1	F	R	D	1	7	Α	4	-N
Options — omit from part number if unwanted  -N = rear control knob for manual positioning  -EQ = internal 512-line magnetic encoder w/ index mark  -EE (1) = remote differential encoder interface; encoder not su	pplie	d											-N

(1) Only available with Plus<sup>2</sup> products.

### IP65-rated products


example part number	K	M	D	Ι	4	М	R	Q	1	7	Α	4	-EQ
QuickStart Kit K = kit option, omit from part number if unwanted	K	М	D	Ι	4	М	R	Q	1	7	Α	4	–EQ
MDrivePlus version MDI = Intelligent — programmable Motion Control	K	М	D	1	4	М	R	Q	1	7	Α	4	–EQ
Input 4 = Plus² version with expanded features	K	М	D	Ι	4	М	R	Q	1	7	Α	4	–EQ
P1 connector M = M23 industrial connectors	K	М	D	Ι	4	М	R	Q	1	7	Α	4	–EQ
Communication type R = RS-422/485	K	М	D	I	4	М	R	Q	1	7	Α	4	–EQ
P2 connector Q = M12 industrial connector	K	М	D	I	4	М	R	Q	1	7	Α	4	–EQ
Motor size 17 = NEMA 17 1.7" / 42mm	K	М	D	I	4	М	R	Q	1	7	А	4	–EQ
Motor length A = single stack B = double stack C = triple stack	K	М	D	I	4	М	R	Q	1	7	Α	4	–EQ
Drive voltage 4 = +12 to +48 VDC	K	М	D	Ι	4	М	R	Q	1	7	Α	4	–EQ
Options — omit from part number if unwanted  -EQ = internal 512-line magnetic encoder w/ index mark  -FE = remote differential encoder interface; encoder not supp	olied												–EQ

# MDI•17 programmable Motion Control


### Motor performance

MD•17 NEMA 17 motor specifications	Motor	Stack length	Single	Double	Triple
	Holding torque	oz-in	32	60	75
		N-cm	23	42	53
	Detent torque	oz-in	1.7	2.1	3.5
	Detent torque	N-cm	1.2	1.5	2.5
	Rotor inertia	oz-in-sec <sup>2</sup>	0.0005	0.0008	0.0012
		kg-cm <sup>2</sup>	0.038	0.057	0.082
	Weight (motor+driver)	OZ	10.4	12.0	15.2
		g	295	340	431


### MD•17 NEMA 17 speed torque (1)







### Triple stack length



Speed of rotation in full steps per second (rpm)

<sup>(1)</sup> Test conditions: 100% current with damper simulating load.